

CW-Endo

Ultrasonic Endo Activation Device

Real-time frequency search

Ultra capacity battery

OLED display



Power levels: T1、T2、T3

Operating time: 10s/20s/30s/45s/60s

Tip vibration frequency: 45kHz±5kHz

Primary tip vibration excursion: <200um

Screen: OLED display (clearly displays such as power and time)



Adapter: AC100-240V,
50/60Hz,DC5V/1A



Dominant hand



Adjustable volume



1600mAh



Adjustable auto-power off time



Restore factory setting



Wrench: 1pc

The wrench sufficiently ensures the consistency of the installation of the work tip.



Insulating sleeve: 1pc



Tips: S20 *2pcs

Ti20 *2pcs

Ti25 *2pcs