

CF-Pack

Gutta Percha Obturation Device



Instant-heating($250^{\circ}\text{C} < 0.25\text{s}$)

Dual trigger button design

PID control algorithm

Mode: F1、F2、F3、F4、F5

Temperature: 90°C 、 120°C 、 150°C 、 160°C 、 180°C 、 200°C 、 220°C 、 250°C

Heat-time: 3s/5s/8s/10s/15s

Cold-time: 3s/5s/10s



Adapter: AC100-240V,50/60Hz,DC5V/1A



Can be placed in any direction for charging



Dominant hand



Restore factory setting



Adjustable volume



Adjustable auto-power off time



2000mAh



40/0.025

50/0.05

60/0.06