

Apex locator

6th Generation Multi-frequency
DSP Technology

AL-Pex



Features

- Measuring accuracy
- Gradual tone reminder
- 3.5inch segment Display

CE
0297



Adapting to various types of root canals



Volume adjustable



1000mAh

Viewing angle

Foldable
(0° - 78°)



Interoperability

Can be connected with
EM-Motor series Endo
Motor



Components



Measuring wire A



1 PCS

File clip



3 PCS

Lip hook



3 PCS

Measuring wire B (Optional)



1 PCS

Tester




1 PCS

Touch probe




1 PCS




When the root canal file is inserted, as the white indicator bar begins to illuminate, there is no tone sound.


As the file tip move towards to apical foramen, it will beep with different tone to remind.



When the file tip reaches the preset reference point, there is a continuous high-frequency tone sound.



As the root canal file is inserted, when the blue indicator bar begins to illuminate, the device emits a low-frequency tone sound.



Once the file tip exceeds the apical foramen, there is another continuous high-frequency tone to remind with "OVER"